

# Eaton STL61A433CH

Catalog Number: STL61A433CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, Six-jaw, Pre-wired test switch, 600 Vac

## General specifications



### Product Name

Eaton meter socket

### Catalog Number

STL61A433CH

### UPC

786685703411

### Product Length/Depth

5.3 in

### Product Height

21.8 in

### Product Width

12.6 in

### Product Weight

25 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

Austin Energy Approved, transformer rated

Type

Transformer rated socket

Amperage Rating

20A

Feed type

Bottom

Number of jaws

Six-jaw

Voltage rating

600 V

Accessories

Pre-wired test switch

Number of sockets

1

Drawings

[Dimensional Drawing - SKT/SW 20A 6T FW ST](#)

Specifications and datasheets

[Eaton Specification Sheet - STL61A433CH](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)