

Eaton SVX050A1-4A1N2

Catalog Number: SVX050A1-4A1N2

Eaton SVX adjustable frequency drive, 50HP, NEMA Type 1/IP21, 480V, FR7, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Varnished Boards



General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX050A1-4A1N2
UPC	Product Length/Depth
782116103911	10.1 in
Product Height	Product Width
24.8 in	9.3 in
Product Weight	Warranty
77.2 lb	2 year
Compliances	Certifications
Contact Manufacturer	IEC 61800-2
	EN 61800-3 Level H
	UL 508C

defaultTaxonomyAttributeLabel

Brake chopper

No brake chopper

Modification

Varnished Boards

Horsepower

50 hp

Frame size

7

Keypad

Alphanumeric

Input

EMC H

Three-phase

Rating

NEMA 1, IP21

Software

Standard

Resources

Application notes

SPI - Variable frequency drives with a common DC bus

Connecting drives to generator supplies

Electromagnetic compatibility (EMC)

Brochures

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

Catalogs

Product Range Catalog Drives Engineering

Product Datasheet - SVX050A1-4A1N2

Eaton's Volume 6—Solid-State Motor Control

Drawings

SVX and SPX Series FR4-FR11 PDF Open Drawings

Installation instructions

9000X AFD User Manual

Specifications and datasheets

Eaton Specification Sheet - SVX050A1-4A1N2



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia