



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



T20P11S50AEE 50KVA XFMR 1PH 240X480-120/240

Eaton Corp

Catalog Number	T20P11S50AEE
Manufacturer	Eaton Corp
Description	Purge-Dry Type Distribution Vent. Transformer, DS-3, Single-Phase, Prim. Voltage: 240 X 480V, Taps: 1 At +5% Fcan, 2 At -5% FCBN X 2 At +2.5% Fcan, 4 At -2.5% FCBN, Sec. Voltage: 120/240V, 150°C, 50 Kva, Al Windings, FR843, 3XA, 60 HZ, Nema
Weight per unit	396.0 (lbs/each)
Product Category	20130517085137

Features

design	DS-3
Primary Voltage	240 x 480V
Secondary Voltage	120/240V

Dimensions and Weight

Height	38.7 IN
Length	34.38 IN
Width	23.51 IN

Descriptions

Description	50KVA XFMR 1PH 240X480-120/240
extra long description	ETN T20P11S50AEE Eaton General purp
Long Description	PURGE-Dry type distribution vent. transformer, DS-3, Single-phase, Prim. voltage: 240 x 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN, Sec. voltage: 120/240V, 150°C, 50 kVA, Al windings, FR843, 3XA, 60 Hz, NEMA
Product Type	Eaton General Purpose Ventilated Transformer

Manufacturer Information

Brand	Eaton
GTIN	00786680109584
Manufacturers Part Number	T20P11S50AEE
UPC	786680109584

Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Dry type distribution, ventilated transformer

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	396



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Power Distribution
Enclosure	NEMA 2
Frequency Rating	60 Hz
standard	UL Listed
Temperature Rating	150°C