



240X480 - 120/240
240 X 480 Primary Volts - 120/240 Secondary Volts - Four Windings - 1Ø
Dry Type Distribution Transformer - Single Phase

1007



Catalog #: T253007S

PRODUCT FEATURES

- UL listed, CSA certified
- Meet CSA C802.2 Efficiency
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|-----------|
| kVA: | 0.25 |
| Primary Voltage: | 240 X 480 |
| Secondary Voltage: | 120/240 |
| Frequency: | 50/60 Hz |
| Max Temperature Rise: | 115°C |
| UL Insulation Class: | 155°C |

PRODUCT MEASUREMENTS

| | |
|------------------|-------------|
| Height (In./cm): | 8.68 (22.0) |
| Width (In./cm): | 4.08 (10.4) |
| Depth (In./cm): | 3.88 (9.9) |

CONFIGURATION

| | |
|---------------------|---------------------|
| Construction Type: | Encapsulated |
| Mounting Type: | Wall |
| Knockouts (In./Cm): | 0.50-0.75 (1.3-1.9) |
| Weather Shield: | WSA7 |
| Wiring Diagram: | 2 |

PACKAGING

Ship Weight (Lbs/Kg): 10 (4.5)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf



240X480 - 120/240
240 X 480 Primary Volts - 120/240 Secondary Volts - Four Windings - 1Ø
Dry Type Distribution Transformer - Single Phase

1007



Catalog #: T253007S

PRODUCT FEATURES

- UL listed, CSA certified
- Meet CSA C802.2 Efficiency
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|-----------|
| kVA: | 0.25 |
| Primary Voltage: | 240 X 480 |
| Secondary Voltage: | 120/240 |
| Frequency: | 50/60 Hz |
| Max Temperature Rise: | 115°C |
| UL Insulation Class: | 155°C |

PRODUCT MEASUREMENTS

| | |
|------------------|-------------|
| Height (In./cm): | 8.68 (22.0) |
| Width (In./cm): | 4.08 (10.4) |
| Depth (In./cm): | 3.88 (9.9) |

CONFIGURATION

| | |
|---------------------|---------------------|
| Construction Type: | Encapsulated |
| Mounting Type: | Wall |
| Knockouts (In./Cm): | 0.50-0.75 (1.3-1.9) |
| Weather Shield: | WSA7 |
| Wiring Diagram: | 2 |

PACKAGING

Ship Weight (Lbs/Kg): 10 (4.5)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf