



240X480 - 120/240
240 X 480 Primary Volts - 120/240 Secondary Volts - Four Windings - 1Ø
Dry Type Distribution Transformer - Single Phase

1007



Catalog #: T253007S

PRODUCT FEATURES

- UL listed, CSA certified
- Meet CSA C802.2 Efficiency
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	0.25
Primary Voltage:	240 X 480
Secondary Voltage:	120/240
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	155°C

PRODUCT MEASUREMENTS

Height (In./cm):	8.68 (22.0)
Width (In./cm):	4.08 (10.4)
Depth (In./cm):	3.88 (9.9)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.50-0.75 (1.3-1.9)
Weather Shield:	WSA7
Wiring Diagram:	2

PACKAGING

Ship Weight (Lbs/Kg): 10 (4.5)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf



240X480 - 120/240
240 X 480 Primary Volts - 120/240 Secondary Volts - Four Windings - 1Ø
Dry Type Distribution Transformer - Single Phase

1007



Catalog #: T253007S

PRODUCT FEATURES

- UL listed, CSA certified
- Meet CSA C802.2 Efficiency
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

UL STANDARD

UL 506

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	0.25
Primary Voltage:	240 X 480
Secondary Voltage:	120/240
Frequency:	50/60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	155°C

PRODUCT MEASUREMENTS

Height (In./cm):	8.68 (22.0)
Width (In./cm):	4.08 (10.4)
Depth (In./cm):	3.88 (9.9)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	0.50-0.75 (1.3-1.9)
Weather Shield:	WSA7
Wiring Diagram:	2

PACKAGING

Ship Weight (Lbs/Kg): 10 (4.5)

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No. 47
CSA Listed: LR7357-32
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf