



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TA874N5 115VAC Horn W/Grille

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | TA874N5   |
| Manufacturer     | Nsi Industries  |
| Description      | Mechanical Horn With A Loud Decibel Output Of Approximately 87DB At 10 Feet. Low Frequency Resonation For Strong Penetration Of Noisy Areas Like Boiler Rooms, Water Pumping Stations, Elevators and Air Compressor Rooms. Steel Housing Painted With Color "Dawn Mist". Grill Design On Cover Facilitates High Sound Output. |
| Weight per unit  | 2.0 (lbs/each)  |
| Product Category | Bells, Horns, Sirens, BZZRS, S  |

### Features

|                     |                            |
|---------------------|----------------------------|
| dimensions          | L=4.437 - H=4.437 - D=.687 |
| Material            | Steel                      |
| Operating Current   | .070 Amps                  |
| Operating Frequency | 60 Hz                      |
| Operating Voltage   | 120 VAC                    |
| Warranty            | 1 YEAR                     |

### Material, Color, and Finish

|       |           |
|-------|-----------|
| Color | DAWN MIST |
|-------|-----------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 115VAC HORN W/GRILLE   |
| extra long description | TORK TA874-N5 Multitone Horn 20-31V  |
| Features               | Tork 120VAC Mechanical Horn APPLICATIONS: Loud tone with typical decibel output of 87 dB at 10 feet. Low frequency resonance for strong penetration of noisy areas like boiler rooms, water pumping stations, elevators and air compressor rooms. FEATURES: INPUT VOLTAGE: 120VAC, 60Hz. Wide input voltage ratings for compatibility with unregulated power supplies. INPUT CURRENT (AMPS): 0.070 WIRING: Screw terminals for convenient IN/OUT wiring. Low current draw for minimizing power supply and wiring cost. HOUSING |
| Long Description       | Mechanical Horn with a loud decibel output of approximately 87dB at 10 feet. Low frequency resonance for strong penetration of noisy areas like boiler rooms, water pumping stations, elevators and air compressor rooms. Steel housing painted with color "Dawn Mist". Grill design on cover facilitates high sound output.   |
| Product Type           | Multitone Horn 20-31VDC Dawn Mist  |
| Special Features       | Loud Tone With Typical Decibel Output of 103 db - Low Frequency Resonation For Strong Penetration Of Noisy Areas   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00786261960238 |
| Manufacturers Part Number | TA874-N5       |
| UPC                       | 786261960238   |

## Taxonomies, Classifications, and Categories

|                      |                     |
|----------------------|---------------------|
| Category Description | SIGNALING EQUIPMENT |
| Type                 | MECHANICAL HORN     |

## Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 2 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Boiler Rooms-Water Pumping Stations-Elevators-Air Compressor Rooms |
| Mounting    | Indoor-Outdoor Box   |
| standard    | UL   |