



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TB3R403 27X16X5 N3R 400A, 600W 4BRS TRML BX *Hoffman Enclosures, Inc.*

Catalog Number	TB3R403
Manufacturer	Hoffman Enclosures, Inc.
Description	Terminal Box 3-Phase Type 3R, 27.00X16.00X5.00, Gray, Steel
Weight per unit	41.2 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

Features

amps	400
ip rating	IP32
Material	MILD STEEL
Phase	3Ø

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Depth	6
Height	27
Size	27.00x16.00x5.00 in
Width	20.5

Descriptions

Description	27X16X5 N3R 400A,600W 4BRS TRML BX
extra long description	NVENT HOF TB3R403 3R Terminal Box 4
Features	Terminal Box, Type 3R are wire-splice boxes for outdoor commercial or industrial applications that have a feeder tap to branch circuits. Boxes are available in three- or four-wire configurations in sizes up to 400 A.
Long Description	Terminal Box 3-Phase Type 3R, 27.00x16.00x5.00, Gray, Steel
Product Type	3R Terminal Box 400 Amp 3 PH

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510144487
Manufacturers Part Number	TB3R403
UPC	783510144487

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Utility / Canadian Cabinets and Splitters



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	41.16

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	3R Weather-resistant, except dust