

DBX/DBXQC/RMNICD

6" Dual Labeled IC/Non-IC AirShield Downlights

LiteBox



DBX shown

Features

DBX/DBXQC/RMNICD:

The DBX is three housing in one. It is IC, Non-IC, and Air Shield rated all in one housing. DBX trims are also dual rated for both IC and Non-IC use. This product is ideal for residential and multi-family applications. All housings are UL/CUL listed and approved for use in damp locations and through wiring.

	DBX/DBXQC	RMNICD
Length	10 ³ / ₄ "	15 ³ / ₈ "
Width	7 ⁷ / ₈ "	6 ⁵ / ₈ "
Height	7 ¹ / ₂ "	7 ¹ / ₂ "
Ceiling Cutout	6 ⁷ / ₈ "	6 ⁵ / ₈ "
Max. Ceiling Thickness	2 ¹ / ₂ "	1 ¹ / ₂ "

Order housing, trim and accessories as separate line items.

Catalog No. Description

Line 1 Order Housing:

- ✳ **DBX** 6", line voltage housing. Dual labeled for IC or non-IC rated new construction applications. Air Shield rated.
- ✳ **DBXQC** 6", line voltage housing. Dual labeled for IC or non-IC rated new construction applications with wiring quick connects. Air Shield rated.
- RMNICD** 6", line voltage remodel housing. Dual labeled for IC or non-IC rated remodel applications.

Catalog No. Description

Catalog No. Description

Line 2 Order Trim:



Adjustable

- TA60** White eyeball. Metal Flange. IC/Non-IC: 75W PAR-30, 65W BR-30
- TA65** Black regressed eyeball. IC: 50W PAR-30, 65W BR-30. Non-IC: 75W PAR-30, 85W BR-30
- TAW65** White regressed eyeball. IC: 50W PAR-30, 65W BR-30. Non-IC: 75W PAR-30, 85W BR-30



Baffle

- TB60** Stepped black baffle. IC: 75W PAR-30, 65W BR-30. Non-IC: 150W PAR-38, 120W BR-40, 40W A-19
- TBW60** Stepped white baffle. IC: 75W PAR-30, 65W BR-30. Non-IC: 150W PAR-38, 120W BR-40, 40W A-19
- TB61** Stepped long-neck black baffle. IC: 75W PAR-30L, 65W BR-30. Non-IC: 75W PAR-30L, 85W BR-30, 100W A-19
- TBW61** Stepped long-neck white baffle. IC: 75W PAR-30L, 65W BR-30. Non-IC: 75W PAR-30L, 85W BR-30, 100W A-19
- TB62** High wattage black stepped baffle. IC: 90W PAR-38, 90W BR-40. Non-IC: 150W PAR-38, 120W BR-40
- TBW62** High wattage white stepped baffle. IC: 90W PAR-38, 90W BR-40. Non-IC: 150W PAR-38, 120W BR-40



Lensed

- TL60** Drop opal shower trim. Non-metallic flange. IC: 50W PAR-30, 40W A-19. Non-IC: 75W PAR-30, 75W A-19
- TL61** Glass drop opal shower trim. IC: 50W PAR-30, 60W A-19. Non-IC: 75W PAR-30, 100W A-19
- TL62** Fresnel shower trim. Non-metallic flange. IC: 50W PAR-30. Non-IC: 75W PAR-30
- TL63** Domed polycarbonate shower trim. IC: 40W A-19. Non-IC: 75W A-19



Lensed (continued)

- TL64** White albalite flush glass shower trim. Metal flange. Non-IC: 75W PAR-30, 60W A-19
- TL65** Textured dome art glass, metal flange in white, polished brass (PB) or Zet Silver (Z).
- TL65PB** IC: 75W PAR-30, 40W A-19. Non-IC: 75W PAR-30, 100W A-19
- TL65Z** IC: 75W PAR-30, 40W A-19. Non-IC: 75W PAR-30, 100W A-19



Open

- TO6** White cone. Metal flange. IC: 75W PAR-30, 65W BR-30. Non-IC: 150W PAR-38, 120W BR-40, 40W A-19
- TO60B** Specular black(B), clear(C) or gold(G) Alzak reflector
- TO60C** IC: 75W PAR-30, 65W BR-30. Non-IC: 150W PAR-38, 120W BR-40, 40W A-19
- TO60G** IC: 75W PAR-30, 65W BR-30. Non-IC: 150W PAR-38, 120W BR-40, 40W A-19
- TO61** White open splay. Metal flange. IC: 75W PAR-30L, 65W BR-30. Non-IC: 75W PAR-30L, 85W BR-30, 100W A-19
- TO62** White open trim. IC: 90W PAR-38, 90W BR-40. Non-IC: 150W PAR-38, 120W BR-40
- TO63WL** White open shower trim. Metal flange. IC/Non-IC: 50W PAR-30L
- TO64WL** White high wattage open shower trim. Metal flange. IC/Non-IC: 75W PAR-38



Wall Wash

- TW61BF** Black baffle wall wash. Max. Non-IC only: 60W A-19
- TW61WBF** White baffle wall wash. Max. Non-IC only: 60W A-19



✳ Denotes Air Shield rated.
 Ⓛ UL Listed for Wet Locations.

6" Compact Fluorescent IC-Rated AirShield Downlights

IBX13ICAT/IBX26ICAT

Features

IBX13ICAT/IBX26ICAT: The IBX13ICAT and IBX26ICAT housings are new Energy Star approved, AirShield rated downlights for use with 13W quad/triple tube or 26W triple/spiral tube compact fluorescent lamps. These products help to provide compliance with model energy codes and qualify for regional utility rebate programs. Both housings use standard LiteBox DBX family trims. Electronic NPF ballast standard. All housings are Energy Star, UL/CUL listed, and are approved for use in damp locations and through wiring.

NEW!

LiteBox



IBX13ICAT shown

Order housing, trim, and accessories as separate line items.

Line 1 Order Housing:

Catalog No.	Description
* IBX13ICAT	6", 13W quad or triple tube CFL IC-Rated housing for new construction where insulation is present. Air Shield™ rated, Energy Star Certified. Lamp Base G24Q-1 (120V)
* IBX26ICAT	6", 26W triple or spiral tube CFL IC-Rated housing for new construction where insulation is present. Air Shield™ rated, Energy Star Certified. Lamp Base G24Q-3 (120V)

Line 2 Order Trim:

Catalog No.	Description	Catalog No.	Description
Baffle			
TB60	Stepped black baffle One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube	TL65PB	• Textured dome art glass shower trim. Polished Brass Metal flange One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
TBW60	Stepped white baffle One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube	TL65Z	• Textured dome art glass shower trim. Zet Metal flange One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
TB61	Stepped black baffle One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube	Open	
TBW61	Stepped white baffle One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube	TO6	White cone. Metal flange. One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
TB62	Deep black baffle One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube	TO60B	Specular black Alzak reflector One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
TBW62	Deep white baffle One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube	TO60C	Specular clear Alzak reflector One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
Lensed			
TL60	• Drop opal shower trim. Non-metallic flange. One 13W or 26W Triple/Spiral Tube	TO60G	Specular gold Alzak reflector One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
TL61	• Glass drop opal shower trim. One 13W or 26W Triple/Spiral Tube	TO61	White open splay. Metal flange. One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
TL62	• Fresnel shower trim. Non-metallic flange. One 13W Triple Tube	TO62	White open trim One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
TL63	• Domed polycarbonate shower trim. One 13W or 26W Triple/Spiral Tube	Wall Wash	
TL64	• White albalite flush glass shower trim. One 13W Quad Tube or Triple Tube, One 13W or 26W Triple Tube	TW61BF	Wall wash, black baffle One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube
TL65	• Textured dome art glass shower trim. White Metal Flange One 13W Quad Tube or Triple Tube, One 13W or 26W Triple/Spiral Tube	TW61WBF	Wall wash, white baffle One 13W Quad Tube, One 13W or 26W Triple/Spiral Tube

Order Accessories:

G6	Ceiling gasket for 6" housings. Ceiling gasket seals housing to drywall opening as an option for Washington State Energy Code (W.S.E.C.) compliance.
----	--



* Denotes Air Shield rated.
• UL Listed for Wet Locations.

6" High Wattage IC-Rated Downlights

IBXHW

LiteBox

Features

IBXHW:

The IBXHW is designed for IC applications where wattages higher than those offered in traditional standard IC cans are required. It utilizes the same trims as the DBX family and is Air Shield rated to comply with air tight requirements in accordance to ASTM E 283. IBXHW is ideal for residential and multi-family applications, is UL/CUL Listed, and approved for use in damp locations and through wiring.

	IBXHW
Length	13"
Width	8 ³ / ₈ "
Height	7 ⁵ / ₈ "
Ceiling Cutout	6 ⁷ / ₈ "
Max. Ceiling Thickness	2"

Order housing, trim, and accessories as separate line items. See ordering example below.

Catalog No. Description

Line 1 Order Housing:

- ✳ IBXHW 6", line voltage high wattage housing for IC rated new construction applications. Air Shield rated.

Catalog No. Description

Catalog No. Description

Line 2 Order Trim:

Adjustable		Open	
	TA60 White eyeball 75W PAR-30L, 85W BR-30		TO6 White cone. Metal flange. 150W PAR-38, 120W BR-40, 100W A-19
	TA65 Black regressed eyeball 75W PAR-30L, 85W BR-30		TO60B Specular black Alzak reflector 150W PAR-38, 120W BR-40, 100W A-19
	TAW65 White regressed eyeball 75W PAR-30L, 85W BR-30		TO60C Specular clear Alzak reflector 150W PAR-38, 120W BR-40, 100W A-19
Baffle		TO60G	
	TB60 Stepped black baffle 150W PAR-38, 120W BR-40, 100W A-19		TO60G Specular gold Alzak reflector 150W PAR-38, 120W BR-40, 100W A-19
	TBW60 Stepped white baffle 150W PAR-38, 120W BR-40, 100W A-19		TO61 White open splay. Metal flange. 75W PAR-30L, 85W BR-30, 75W A-19
	TB61 Stepped long-neck black baffle 75W PAR-30L, 75W BR-30, 75W A-19		TO62 White open trim 150W PAR-38, 120W BR-40
	TBW61 Stepped long-neck white baffle 75W PAR-30L, 75W BR-30, 75W A-19	Open Shower	
	TB62 Stepped black baffle 150W PAR-38, 120W BR-40		TO63WL  White open shower trim. 50W PAR-30L
	TBW62 Stepped white baffle 150W PAR-38, 120W BR-40		TO64WL  High wattage white open shower trim. 75W PAR-38
Lensed		Wall Wash	
	TL60  Drop opal shower trim. Non-metallic flange. 75W PAR-30, 60W A-19		TW61BF Wall wash, black baffle 40W A-19
	TL61  Glass drop opal shower trim. 75W PAR-30, 75W A-19		TW61WBF Wall wash, white baffle 40W A-19
	TL62  Fresnel shower trim. Non-metallic flange. 75W PAR-30		
	TL63  Domed polycarbonate shower trim. 60W A-19		
	TL64  White albalite flush glass shower trim. 40W A-19		

Order Accessories:

- G6**  Ceiling gasket for 6" housings. Ceiling gasket seals housing to drywall opening as an option for Washington State Energy Code (W.S.E.C.) compliance.

✳ Denotes Air Shield rated.
 UL Listed for Wet Locations.