



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC612 3/4" Emt Concrete Tight D/C Coupling

Appleton/Oz Gedney

Catalog Number	TC612
Manufacturer	Appleton/Oz Gedney
Description	Features:Concretetight, Application:Dry/Damp Location, Standard:UL 514B, Csa C22.2, Nema FB-1, Trade Size:0.75IN, Outside Diameter:1.21IN, Length:1.78IN, Material:Zinc Die Cast
Weight per unit	0.1600 (lbs/each)
Product Category	Die Cast Compression Emt CPLG

Features

Connector Type	Compression
Material	Zinc Die Cast
outside diameter	1.21

Material, Color, and Finish

Color	Metallic
-------	----------

Dimensions and Weight

Length	1.78
--------	------

Descriptions

Description	3/4" EMT CONCRETE TIGHT D/C COUPLING
extra long description	EGS TC-612 3/4 IN EMT COMP CPLG ZNC
Long Description	Features:Concretetight, Application:Dry/Damp Location, Standard:UL 514B, CSA C22.2, NEMA FB-1, Trade Size:0.75IN, Outside Diameter:1.21IN, Length:1.78IN,Material:Zinc Die Cast
Product Type	3/4 In Emt Comp CPLG ZNC D/C
Special Features	Concretetight

Manufacturer Information

Brand	Appleton
GTIN	00687855106127
Manufacturers Part Number	TC-612
UPC	687855106127

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	EMT Conduit Compression Coupling

Trade Size

Trade Size	0.75
------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Package	250
Weight Per each	0.16

Uses, Certifications, and Standards

Application	To join lengths of steel EMT for concretetight, dry or damp locations
standard	UL 514B, UL Listed E35001, CSA C22.2 No. 18.3 CSA Certified 208044, NEMA FB-1