Specifications







Eaton TCF60

Eaton Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 60 A, indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac

General specifications	
PRODUCT NAME	Eaton Bussmann series TCF fuse
CATALOG NUMBER	TCF60
UPC	051712615082
EAN	5027590184441
PRODUCT LENGTH/DEPTH	2.13 in
PRODUCT HEIGHT	1.9 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.17 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified

Powering Business Worldwide

Electrical rating

AMPERAGE RATING	60 A
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
INTERRUPT RATING	300 kAIC at 600 Vac 100 kAIC at 300 Vdc
RESPONSE TIME	10 sec at 500%
VOLTAGE RATING	600 Vac, 300 Vdc

Physical details

COLOR	Black
FUSE TYPE	Class CF Time delay
MATERIAL	Glass filled PES
NUMBER OF ELEMENTS	Dual
PACKAGING TYPE	Standard

General information

CLASS	Class CF
CONNECTION	Blade end
FUSE INDICATOR	With Indicator
MOUNTING METHOD	Chassis 35 mm DIN rail
SPECIAL FEATURES	Finger safe
USED WITH	TCFH60N, CCP2-3-60CF

Resources

CATALOGS	Low Voltage Branch Circuit Fuse Chapter Bussmann Full Line Catalog
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	The Power of Space Bussmann series Fuseology
TECHNICAL DATA SHEETS	Bussmann series UL Class CF CUBEFuse data sheet no. 9000

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

Specifications







Eaton TCF60

Eaton Bussmann Series Class CF fuse, TCF, time-delay, dual-element current limiting cube fuse, 60 A, indicating fuse, interrupting rating of 100 kA at 300 Vdc and 300 kA at 600 Vac

General specifications	
PRODUCT NAME	Eaton Bussmann series TCF fuse
CATALOG NUMBER	TCF60
UPC	051712615082
EAN	5027590184441
PRODUCT LENGTH/DEPTH	2.13 in
PRODUCT HEIGHT	1.9 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.17 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified

Powering Business Worldwide

Electrical rating

AMPERAGE RATING	60 A
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
INTERRUPT RATING	300 kAIC at 600 Vac 100 kAIC at 300 Vdc
RESPONSE TIME	10 sec at 500%
VOLTAGE RATING	600 Vac, 300 Vdc

Physical details

COLOR	Black
FUSE TYPE	Class CF Time delay
MATERIAL	Glass filled PES
NUMBER OF ELEMENTS	Dual
PACKAGING TYPE	Standard

General information

CLASS	Class CF
CONNECTION	Blade end
FUSE INDICATOR	With Indicator
MOUNTING METHOD	Chassis 35 mm DIN rail
SPECIAL FEATURES	Finger safe
USED WITH	TCFH60N, CCP2-3-60CF

Resources

CATALOGS	Low Voltage Branch Circuit Fuse Chapter Bussmann Full Line Catalog
COMPLIANCE INFORMATION	RoHS Search Tool
MULTIMEDIA	The Power of Space Bussmann series Fuseology
TECHNICAL DATA SHEETS	Bussmann series UL Class CF CUBEFuse data sheet no. 9000

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.