



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TDP43ME 300DPI Desktop Printer

*Panduit Corporation*

Catalog Number	TDP43ME
Manufacturer	Panduit Corporation
Description	The TDP43ME Desktop Printer For North American Usage Has 300 Dpi Resolution and 4" Per Second Maximum Print Speed. Print A Variety Of Self-Laminating Labels, Component Labels, Non-Laminated Labels, Heat-Shrink Labels, Marker Plates, and Continuous Tapes Up to 4" Wide. It Includes Easy-Mark Plus Labeling Software, RMEH4BL Black Hybrid Ribbon, A Usb Cable, A User Manual, A Quick Start Card, A Driver Disk, and A Us Power Cord. 6.8" X 8.9" (173 MM X 226 MM). 6 Pounds. Color Black/Gray.
Weight per unit	10.3 (lbs/each)
Product Category	CBL Marking & Labeling Equip

### Features

media	Yes
Resolution	300

### Descriptions

Description	300DPI DESKTOP PRINTER
extra long description	PAN TDP43ME TDP43ME Desktop Printer
Long Description	The TDP43ME Desktop Printer for North American usage has 300 dpi resolution and 4" per second maximum print speed. Print a variety of self-laminating labels, component labels, non-laminated labels, heat-shrink labels, marker plates, and continuous tapes up to 4" wide. It includes Easy-Mark Plus Labeling Software, RMEH4BL black hybrid ribbon, a USB cable, a user manual, a quick start card, a driver disk, and a US power cord. 6.8" x 8.9" (173 mm x 226 mm). 6 pounds. Color Black/Gray.
Product Type	TDP43ME Desktop Printer, 300 Dpi, 4 In/S Print Speed, PK1

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983319084
Manufacturers Part Number	TDP43ME
UPC	074983319084

### Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	Desktop Printer



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	5
Package	1
Weight Per each	10.3

## Uses, Certifications, and Standards

Application	NA
standard	RoHS Compliant