

# NEER Straps

For Rigid Conduit and IMC.

## 1800: One Hole Click-On

### Applications

- Click-on type one hole straps for rigid conduit or IMC.
- Provides support for the conduits, as required by the National Electrical Code.

### Material/Finish

- Steel/zinc plated

## TH-1800: Two Hole Snap-On

### Applications

- Snap-on type two hole straps for rigid conduit and IMC are used where higher load bearing supports are desired.


### Material/Finish

- Steel/zinc plated


### Certifications and Compliances

- UL Standard: 2239
- UL Listed: E333806
- CSA Standard: C22.2 No. 18.4
- cUL Listed: E333806

COMMERCIAL PRODUCTS: RIGID AND IMC FITTINGS



1801



TH-1801

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters			
		A	B	C	D
1/2	<b>1801</b>	1.85/47.0	0.80/20.3	0.62/15.7	0.25/6.4
3/4	<b>1802</b>	1.22/31.0	0.92/23.4	0.75/19.1	0.25/6.4
1	<b>1803</b>	2.65/67.3	1.15/29.2	0.87/22.1	0.31/7.9
1-1/4	<b>1804</b>	2.98/75.7	1.41/35.8	0.99/25.1	0.38/9.7
1-1/2	<b>1805</b>	3.51/89.2	1.61/40.9	1.00/25.4	0.44/11.2
2	<b>1806</b>	4.17/105.9	1.97/50.0	1.14/29.0	0.53/13.5
2-1/2	<b>1807</b>	4.99/126.7	2.85/72.4	1.24/31.5	0.53/13.5
3	<b>1808</b>	5.55/141.0	3.47/88.1	1.25/31.8	0.53/13.5
3-1/2	<b>1809</b>	6.25/158.8	4.10/104.1	1.25/31.8	0.53/13.5
4	<b>1810</b>	7.00/177.8	4.51/114.6	1.26/32.0	0.53/13.5

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters			
		A	B	C	D
1/2	<b>TH-1801</b>	2.47/62.7	0.86/21.8	0.62/15.7	0.19/4.8
3/4	<b>TH-1802</b>	2.82/71.6	1.10/27.9	0.68/17.3	0.19/4.8
1	<b>TH-1803</b>	3.38/85.9	1.27/32.3	0.75/19.1	0.25/6.4
1-1/4	<b>TH-1804</b>	4.00/101.6	1.68/42.7	0.86/21.8	0.25/6.4
1-1/2	<b>TH-1805</b>	4.24/107.7	1.67/42.4	0.87/22.1	0.25/6.4
2	<b>TH-1806</b>	4.44/112.8	1.98/50.3	0.94/23.9	0.38/9.7
2-1/2	<b>TH-1807</b>	5.19/131.8	2.87/72.9	0.98/24.9	0.38/9.7
3	<b>TH-1808</b>	6.37/161.8	3.56/90.4	0.99/25.1	0.38/9.7
3-1/2	<b>TH-1809</b>	7.37/187.2	4.05/102.9	1.00/25.4	0.44/11.2
4	<b>TH-1810</b>	8.12/206.2	4.51/114.6	1.00/25.4	0.44/11.2

# NEER Straps

For Rigid Conduit and IMC.

## 1800: One Hole Click-On

### Applications

- Click-on type one hole straps for rigid conduit or IMC.
- Provides support for the conduits, as required by the National Electrical Code.

### Material/Finish

- Steel/zinc plated

## TH-1800: Two Hole Snap-On

### Applications

- Snap-on type two hole straps for rigid conduit and IMC are used where higher load bearing supports are desired.

### Material/Finish

- Steel/zinc plated

### Certifications and Compliances


- UL Standard: 2239
- UL Listed: E333806
- CSA Standard: C22.2 No. 18.4
- cUL Listed: E333806

COMMERCIAL PRODUCTS: RIGID AND IMC FITTINGS


Commercial Products



1801



TH-1801



Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters			
		A	B	C	D
1/2	1801	1.85/47.0	0.80/20.3	0.62/15.7	0.25/6.4
3/4	1802	1.22/31.0	0.92/23.4	0.75/19.1	0.25/6.4
1	1803	2.65/67.3	1.15/29.2	0.87/22.1	0.31/7.9
1-1/4	1804	2.98/75.7	1.41/35.8	0.99/25.1	0.38/9.7
1-1/2	1805	3.51/89.2	1.61/40.9	1.00/25.4	0.44/11.2
2	1806	4.17/105.9	1.97/50.0	1.14/29.0	0.53/13.5
2-1/2	1807	4.99/126.7	2.85/72.4	1.24/31.5	0.53/13.5
3	1808	5.55/141.0	3.47/88.1	1.25/31.8	0.53/13.5
3-1/2	1809	6.25/158.8	4.10/104.1	1.25/31.8	0.53/13.5
4	1810	7.00/177.8	4.51/114.6	1.26/32.0	0.53/13.5

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters			
		A	B	C	D
1/2	TH-1801	2.47/62.7	0.86/21.8	0.62/15.7	0.19/4.8
3/4	TH-1802	2.82/71.6	1.10/27.9	0.68/17.3	0.19/4.8
1	TH-1803	3.38/85.9	1.27/32.3	0.75/19.1	0.25/6.4
1-1/4	TH-1804	4.00/101.6	1.68/42.7	0.86/21.8	0.25/6.4
1-1/2	TH-1805	4.24/107.7	1.67/42.4	0.87/22.1	0.25/6.4
2	TH-1806	4.44/112.8	1.98/50.3	0.94/23.9	0.38/9.7
2-1/2	TH-1807	5.19/131.8	2.87/72.9	0.98/24.9	0.38/9.7
3	TH-1808	6.37/161.8	3.56/90.4	0.99/25.1	0.38/9.7
3-1/2	TH-1809	7.37/187.2	4.05/102.9	1.00/25.4	0.44/11.2
4	TH-1810	8.12/206.2	4.51/114.6	1.00/25.4	0.44/11.2