



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



THHN40RD2500 THHN 4/0 STR Red 2500' *Southwire Company*

Catalog Number	THHN40RD2500
Manufacturer	Southwire Company
Description	600 Volts. Copper Conductor. Thermoplastic Insulation/Nylon Sheath, Heat, Moisture, Gasoline and Oil Resistant li. Rated THHN and THWN-2. Also Rated MTW. Simpull Technology For Easier Pulling.
Weight per unit	0.7170 (lbs/ft)
Product Category	Wire

Features

Conductor Size	4/0
media	Yes
Number of Conductors	1
Voltage Rating	600

Material, Color, and Finish

Insulation Material	PVC
Jacket Material	Nylon

Dimensions and Weight

Length	2500
--------	------

Descriptions

Description	THHN 4/0 STR RED 2500'
extra long description	SWC 55612904 THHN 4/0 Str Cu SIM Rd
Features	Southwire® SIMpull THHN copper conductors are primarily used in conduit and cable trays for services, feeders and branch circuits in commercial or industrial applications as specified in the National Electrical Code. Voltage for all applications is 600 volts. SIMpull THHN copper conductors are designed to be installed without application of a pulling lubricant.
Long Description	600 Volts. Copper Conductor. Thermoplastic Insulation/Nylon Sheath, Heat, Moisture, Gasoline and Oil Resistant II. Rated THHN and THWN-2. Also rated MTW. SIMpull Technology for Easier Pulling.
Product Type	THHN 4/0 STR Cu Sim RD 2500R
Special Features	No Lube

Manufacturer Information

Brand	Copper
GTIN	00032886913686
Manufacturers Part Number	55612904
UPC	032886913686



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description BUILDING WIRE

Type THHN-2

Availability

minimum qty 2500

Packaging

Carton 2500

Weight Per foot 0.717

Uses, Certifications, and Standards

Application Commerical