



Representative Image

Catalog No. THQMV200NRE

Description: TYPE 3R ENCL W/ BKR 200A SURFACE

UPC No 783164277616

Home > Circuit Breakers > Circuit Breaker Enclosures

PowerMark Gold 200 Amp 10 in. Enclosed Outdoor Circuit Breaker

- Outdoor NEMA 3R Enclosure
- 200A circuit breaker is factory installed
- Short circuit ratings equal to installed breaker rating

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker.

Enclosure notes and/or limitation: Includes factory installed 200 amp 2 pole breaker.

ACCESSORIES:

Neutral Kit (non-GF applications):included
Raintight Hubs: TC150, TC200, TC250, TCCP

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B3

Specifications

Enclosure Type	NEMA Type 3R
Mounting	Surface
Frame Type	Q-Line
Amperage	200 A
Material	Steel
GSA Compliance	No

Classifications

UL/CUL Listing	cULus
----------------	-------

Dimensions

Height	21.0 in
Depth	4.4 in
Width	9.0 in
Weight	18.3 lb



Representative Image

Catalog No. THQMV200NRE

Description: TYPE 3R ENCL W/ BKR 200A SURFACE

UPC No 783164277616

Home > Circuit Breakers > Circuit Breaker Enclosures

PowerMark Gold 200 Amp 10 in. Enclosed Outdoor Circuit Breaker

- Outdoor NEMA 3R Enclosure
- 200A circuit breaker is factory installed
- Short circuit ratings equal to installed breaker rating

GE's circuit breaker enclosures are UL Listed, CSA Certified and are suitable for use as service equipment (except as noted). The short circuit rating of the enclosure/circuit breaker combination is equal to the short circuit rating of the installed circuit breaker.

Enclosure notes and/or limitation: Includes factory installed 200 amp 2 pole breaker.

ACCESSORIES:

Neutral Kit (non-GF applications):included
Raintight Hubs: TC150, TC200, TC250, TCCP

Descriptors

Category	Circuit Breaker Enclosures
GO Schedule	B3

Specifications

Enclosure Type	NEMA Type 3R
Mounting	Surface
Frame Type	Q-Line
Amperage	200 A
Material	Steel
GSA Compliance	No

Classifications

UL/CUL Listing	cULus
----------------	-------

Dimensions

Height	21.0 in
Depth	4.4 in
Width	9.0 in
Weight	18.3 lb