ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TLP128TTUSBB 12-Outlet Surge Protector Power Power Strip 8 FT

Eaton Power Quality

Catalog Number	TLP128TTUSBB
Manufacturer	Eaton Power Quality
Description	Protect It! 12-Outlet Surge Protector, 8 FT. (2.43 M) Cord, 4320 Joules, Tel/Modem/Coax Protection, 2 Usb Ports, Black
Weight per unit	N/A
Product Category	20261002132244

Features

Input Voltage	120V AC
Material	Plastic
nominal voltage	120V AC
Number of Outlets	(12) 5-15R
Outlet	NEMA 5-15P
Plug Type	NEMA 5-15P
Voltage Rating	120V AC V
Wattage	1800 W

Material, Color, and Finish

Color	Black

Dimensions and Weight

Depth	1.380
Height	13.58
Width	7.87

Descriptions

Description	12-OUTLET SURGE PROTECTOR POWER POWER STRIP 8 FT
extra long description	TRP TLP128TTUSBB TLP128TTUSBB
Long Description	Protect It! 12-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 4320 Joules, Tel/Modem/Coax Protection, 2 USB Ports, Black
Product Type	Tlp128ttusbb
Special Features	12-Socket Surge Protector Safeguards Your Sensitive Electronics Ideal for your home or office workstation, this Protect It!® 12-outlet surge protector features a surge protection rating of 4320 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP128TTUSBB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton Power Quality
GTIN	00037332209788
Manufacturers Part Number	TLP128TTUSBB
UPC	037332209788

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Surge protector

Packaging

Carton	1
Weight	1.860 LB
Weight Per each	0

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Mounting	1
standard	UL 1449 ,cUL Listed ,CSA Std. C22.2 ,NOM ,UL Listed ,CSA C22.2.,FCC Part 68 ,RoHS
Temperature Rating	32° to 104°F (0° to 40°C)