



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMCX0752 3/4" Cable Gland

Crouse-Hinds

Catalog Number	TMCX0752
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Terminator II TMCX Cable Gland, TSC Compound, Cable Range:0.65-1.18", Cable Sealing:2 (M), Metal-Cladcorrugated Armoured, Teck Armoured, Armoured Barrier and Tray Cable, Armoured Gland, Aluminum, 3/4" NPT
Weight per unit	0.9500 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Cable OD 0.65 to 1.18 inch
dimensions	4.1800 IN X 2.2500 IN X 2.2500 IN

Material, Color, and Finish

Color	Natural with red union nut
Finish	Untreated

Dimensions and Weight

Size	3/4" NPT, Size 2
------	------------------

Descriptions

Description	3/4" CABLE GLAND
extra long description	CRS-H TMCX075 2 BARR GLAND 3/4 NPT
Features	TMCX II explosionproof cable glands from Eaton Crouse-Hinds Division are used to terminate armoured barrier, non-armoured barrier and TECK armoured cable in hazardous locations. Its unique design features, coupled with our fast curing Chico LiquidSeal compound, make the TMCX II the easiest and safest solution available.
Long Description	Eaton Crouse-Hinds series Terminator II TMCX cable gland,TSC compound,Cable Range:0.65-1.18",Cable Sealing:2 (M),Metal-cladcorrugated armoured,TECK armoured,armoured barrier and tray cable,Armoured gland, Aluminum, 3/4" NPT
Product Type	Barr Gland 3/4 NPT SZ2 Alu TSC
Special Features	2 Piece Union Design

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662276298118
Manufacturers Part Number	TMCX075 2
UPC	662276298118



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description CORD CONNECTORS & CORD GRIPS
Type Cable gland

Packaging

Carton 1
Weight Per each 0.95

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Industrial Facilities/Factories - Other
Mounting 3/4 inch NPT
standard UL and cUL Class 1, Div 1 (ABCD) Class 2 (EFG)
Temperature Rating -40 to + 60 Degrees C