

TP1610F

by Burndy
Catalog ID: TP1610F

Prop 65 Notice

Fork Tongue Copper Terminal, 22-16 Max. Insul. Dia. Accom.: .145 Color Code: Red, 8-10, .95 in L, .41 in W, Polyvinylchloride Insulation.

Features: The Type TP-F Is A Fork Tongue Variation Of The TP Design And Makes Installation Easier, 600 V Maximum, 105 DEG C Max, Fork Tongue Design: Faster Installation-Screw Needs Only To Be Loosened For Termination, Installation Tool: Plier Type: Y10-22 Tool, Ratchet: MR8-89-1 Tool, Insulation Diameter (maximum): 0.145 IN, Bulk Catalog Number: BA16EF10, Tape Mounted Catalog Number: BA16EF10M, Temperature Rating: 105 DEG C Maximum, Color Code: Red, Wire Strip Length: 13/64 IN, Finish: Electro-Tin Plated, Wire Insulation Grip: No



Product Details

General

Application	For Commercial And Light Duty Industrial Control And Power Circuit Applications
Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUK
Trade Name	VINYLUK™
Type	TP-F
UPC	781810714881
UPC 12 Digit	7818107148811

Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	1/4 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.31 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG
Conductor Range	#20 AWG to #22 AWG; 16 AWG to 18 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)