



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TP23 Trademaster Wallplate 2G Blank Box Mount

*Pass & Seymour/Legrand*

Catalog Number	TP23
Manufacturer	Pass & Seymour/Legrand
Description	The Trademaster 2-Gang Blank Wall Plate Is Constructed From High-Impact, Injection Molded Nylon Plastic. Oversized In Height and Width By 3/16THS Of An Inch, This Plate Could Completely Cover An Opening In A Wall That A Standard Plate Fails to Conceal.
Weight per unit	0.1015 (lbs/each)
Product Category	Wall Plates & Covers

### Features

cutout	Blank
indoor/outdoor	Indoor
insulation	Bare
Mounting Type	Box Mounted
Number of Gangs	2
orientation	Vertical
Wall Plate Type	Blank

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	5.5"
Thickness	0.07

### Descriptions

Construction	Plastic
Description	TRADEMASTER WALLPLATE 2G BLANK BOX MOUNT
extra long description	P&S TP23 TRADEMASTER PLT 2G BLANK B
Long Description	The Trademaster 2-gang blank wall plate is constructed from high-impact, injection molded nylon plastic. Oversized in height and width by 3/16ths of an inch, this plate could completely cover an opening in a wall that a standard plate fails to conceal.
Product Type	Trademaster PLT 2G Blank Box Mount
Special Features	Molded of rugged, practically indestructible nylon



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007274905
Manufacturers Part Number	TP23
UPC	785007274905

## Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	Wall Plate

## Packaging

Carton	20
Package	200
Weight Per each	0.1015

## Uses, Certifications, and Standards

Application	Residential/Commercial
Mounting standard	WALL CULUS, CSA, UL514