


Eaton TP246

Catalog Number: TP246

Eaton Crouse-Hinds series Switch Box, (1) 1/2", S, set 7/8", 2, AC/MC clamps, 3-1/2", (1) 1/2", Steel, (2) 1/2", Gangable, 18.0 cubic inch capacity



General specifications

| | |
|--------------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series switch box | TP246 |
| UPC | Product Length/Depth |
| 786189102468 | 2 in |
| Product Height | Product Width |
| 3 in | 3.5 in |
| Product Weight | |
| 0.88 lb | |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

3-1/2"

Type

Gangable

Capacity

18 cubic in

Conduit/cable

AC/MC clamps

Bracket style

S, Set 7/8"

End Knockouts

(1) 1/2 in

Side knockouts

(2) 1/2 in

Bottom Knockouts

(1) 1/2 in

Cable knockouts

2

Material

Steel

Resources

Catalogs

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

Certification reports

[Steel Switch Boxes UL certification](#)

[Steel Switch Boxes Canadian certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP246](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.




[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP246

Catalog Number: TP246

Eaton Crouse-Hinds series Switch Box, (1) 1/2", S, set 7/8", 2, AC/MC clamps, 3-1/2", (1) 1/2", Steel, (2) 1/2", Gangable, 18.0 cubic inch capacity



General specifications

| | |
|--------------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series switch box | TP246 |
| UPC | Product Length/Depth |
| 786189102468 | 2 in |
| Product Height | Product Width |
| 3 in | 3.5 in |
| Product Weight | |
| 0.88 lb | |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

3-1/2"

Type

Gangable

Capacity

18 cubic in

Conduit/cable

AC/MC clamps

Bracket style

S, Set 7/8"

End Knockouts

(1) 1/2 in

Side knockouts

(2) 1/2 in

Bottom Knockouts

(1) 1/2 in

Cable knockouts

2

Material

Steel

Resources

Catalogs

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

Certification reports

[Steel Switch Boxes UL certification](#)

[Steel Switch Boxes Canadian certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP246](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)