

Specifications



Photo is representative

Eaton TP278

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 1-1/2", Steel, (2) 1/2", (2) 3/4", Fixture rated, 15.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series octagon outlet box
CATALOG NUMBER	TP278
UPC	786189102789
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	1.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.5 lb



Certifications and compliances

AREA CLASSIFICATION Ordinary/Non-Hazardous

Product specifications

BOX SIZE 4"

	Locations
STANDARDS TYPE	NEC/CEC

DEPTH	1-1/2"
CAPACITY	15.5 cubic in
CONDUIT/CABLE	Conduit (no clamps)
SIDE KNOCKOUTS	(2) 1/2 in, (2) 3/4 in
BOTTOM KNOCKOUTS	(3) 1/2 in, (2) 3/4 in
MATERIAL	Steel
SPECIAL FEATURES	Fixture rated

Resources

CATALOGS

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

CERTIFICATION REPORTS

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

SPECIFICATIONS AND DATASHEETS

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP278](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

Reserved.

