

Eaton TP290

Catalog Number: TP290

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 2-1/8", Steel, (4) 3/4", Fixture rated, 21.5 cubic inch capacity



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series octagon outlet box	TP290
	UPC
	786189102901
Product Length/Depth	Product Height
4 in	2.13 in
Product Width	Product Weight
4 in	0.64 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Depth

2-1/8"

Capacity

21.5 cubic in

Conduit/cable

Conduit (no clamps)

Side knockouts

(4) 3/4 in

Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

Material

Steel

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP290](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP290

Catalog Number: TP290

Eaton Crouse-Hinds series Octagon Outlet Box, (3) 1/2", (2) 3/4", 4", Conduit (no clamps), 2-1/8", Steel, (4) 3/4", Fixture rated, 21.5 cubic inch capacity

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series octagon outlet box	TP290
	UPC
	786189102901
Product Length/Depth	Product Height
4 in	2.13 in
Product Width	Product Weight
4 in	0.64 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Depth

2-1/8"

Capacity

21.5 cubic in

Conduit/cable

Conduit (no clamps)

Side knockouts

(4) 3/4 in

Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

Material

Steel

Special features

Fixture rated

Resources

Catalogs

[Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page](#)

Certification reports

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification](#)

[Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification](#)

Specifications and datasheets

[Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP290](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)