



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR40R 250V 40A 3X13/16 RK5 TD Fuse

Mersen Fuses

Catalog Number	TR40R
Manufacturer	Mersen Fuses
Description	Power Fuse, Time Delay Fuse Speed, Class RK5 Fuse, 40 A, 250 V Ac;250 V DC, Fiber Glass (Body) Material, 13/16 In Diameter, 3 In Overall Length, Blown Fuse Indicator
Weight per unit	0.1350 (lbs/each)
Product Category	Current Limiting

Features

AC Voltage Rating	250
amperage rating	40
class	Class RK5
connection	Ferrule

Material, Color, and Finish

Body Material	PolyTube
---------------	----------

Dimensions and Weight

Size	3 x 0.81
------	----------

Descriptions

Description	250V 40A 3X13/16 RK5 TD FUSE
extra long description	Mersen TR40R Fuse TR-R - Class RK5
Special Features	Time-delay Current-limiting AC & DC rated Optional solid state SmartSpot blown fuse indicator Time-delay for motor start-ups and transformer inrush currents without nuisance opening Current-limiting for low peak let-thru current Rejection-style design prevents replacement errors (when used with recommended fuse blocks) Easy-to-read label for quick brand recognition and replacement Metal-embossed date and catalog number for traceability and lasting identification Fiberglass body provides dimensional stability

Manufacturer Information

Brand	Mersen
GTIN	00782001747916
UPC	782001747916

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	CLASS RK5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.135

Uses, Certifications, and Standards

Mounting	Clip
standard	UL listed to standard 248-12 File E2137 CSA certified to standard C22.2 no. 248.12 DC listed to UL standard 248 TRS only