



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5251W SGL Recp TR 15A/125V WH

Pass & Seymour/Legrand

Catalog Number	TR5251W
Manufacturer	Pass & Seymour/Legrand
Description	Single Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #10 Awg Compatible Wire Size, Back and Side Wired Connection, Wall Mount, 1.296 In Length, 1.190 In Width, 3.28 In Height, Nylon Material, White, Heavy Duty Corrosion Resistant, 0.1800 LB
Weight per unit	0.1780 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Back and side wire
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
media	Yes
Outlet Type	Indoor, Tamper-Resistant, Commercial
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 10

Material, Color, and Finish

Finish	Matte
--------	-------

Descriptions

Description	SGL RECP TR 15A/125V WH
extra long description	P&S TR5251W RECEP SGL TAMPER RESIS

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007241938
Manufacturers Part Number	TR5251W
UPC	785007241938

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	100
Weight Per each	0.178

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
standard	CULUS, UL498, CSA C22.2 No. 42
Temperature Rating	-40° - 60° C