



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TR5261USBGRY Disc Sub Tr5262usbgry

*Pass & Seymour/Legrand*

Catalog Number	TR5261USBGRY
Manufacturer	Pass & Seymour/Legrand
Description	Decorator Combination 15A 125V Tamper-Resistant Outlet With Two Usb Chargers - Gray
Weight per unit	0.3153 (lbs/each)
Product Category	Wiring Devices

### Features

amperage rating	15
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
media	Yes
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wire Size	14 - 10

### Dimensions and Weight

Depth	1.31
Height	4.18
Width	1.60

### Descriptions

Description	DISC SUB TR5262USBGRY
extra long description	P&S TR5261USBGRY DISC SUB TR5262USB
Long Description	Decorator Combination 15A 125V Tamper-Resistant Outlet with Two USB Chargers - Gray
Product Type	Disc Sub Tr5262usbgry
Special Features	Designed for commercial markets with strength and durability in mind, this combination USB charger receptacle features 2.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007029055
Manufacturers Part Number	TR5261USBGRY
UPC	785007029055

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Tamper-Resistant USB Single Receptacle



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Amperage ..... 15.0

## Availability

Status ..... Inactive

## Packaging

Carton ..... 10

Package ..... 50

Weight Per each ..... 0.3153

## Uses, Certifications, and Standards

Application ..... Commercial

environmental conditions ..... UL94 V2

Mounting ..... BOX

nema rating ..... 5-15R

standard ..... CSA Listed, ETL Lsted, FSUL, UL Listed, RoHS