



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TR5361USBBK Disc Sub Tr5362usbbk *Pass & Seymour/Legrand*

Catalog Number	TR5361USBBK
Manufacturer	Pass & Seymour/Legrand
Description	Decorator Combination 20A 125V Tamper-Resistant Outlet With Two Usb Chargers - Black
Weight per unit	0.3170 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	20
connection	Side & Back Wired
Dielectric Strength	Withstands 2000V minimum
Number of Wires	3
Phase	1
Poles	2
Voltage Rating	125
Wire Size	14 -10

Dimensions and Weight

Depth	1.31
Height	4.18
Width	1.60

Descriptions

Description	DISC SUB TR5362USBBK
extra long description	P&S TR5361USBBK 20A TR SPEC GRD W/2
Long Description	Decorator Combination 20A 125V Tamper-Resistant Outlet with Two USB Chargers - Black
Product Type	20A TR Spec GRD W/2.1A Usb CHRG BK
Special Features	Designed for commercial markets with strength and durability in mind, this combination USB charger receptacle features 2.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007029109
Manufacturers Part Number	TR5361USBBK
UPC	785007029109

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Tamper-Resistant USB Single Receptacle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Package 50

Weight Per each 0.317

Uses, Certifications, and Standards

Application Commercial

environmental conditions UL94 V2

Mounting BOX

nema rating 5-20R

standard CSA Listed, ETL Lsted, FSUL, UL Listed, RoHS