



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TRIURD404040PCS Tri Urd 4/0 4/0 4/0 Monm Alu PCS

King Wire Inc.

Catalog Number	TRIURD404040PCS
Manufacturer	King Wire Inc.
Description	Type MC Cable, Flame Retardant;Sunlight Resistant Additional Information, Wet/Dry and Interior Wiring Application, Aluminum Alloy Conductor Material, 4/0-4/0-4/0 Awg Conductor Size, 205 A Current Rating, Polyethylene Insulation Material, Metal Free Polyvinyl Chloride (PVC) Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 19 (Phase) - Conductors, 0.857 X 1.445 In Outside Diameter, Strand Solid/Strand, Directive 2002/95/Ec;Federal Specification JC-30B Nec;Nec Nfpa 70, 2011 Edition;Rohs Com
Weight per unit	0.8280 (lbs/ft)
Product Category	Seu

Descriptions

Description	TRI URD 4/0 4/0 4/0 MONM ALU PCS
-------------	----------------------------------

Manufacturer Information

Brand	Aluminum
-------	----------

Taxonomies, Classifications, and Categories

Category Description	Direct Burial Wire
----------------------	--------------------

Packaging

Carton	1
Weight Per foot	0.828