



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TY523MX 3.62" "Ty-Rap" Cable Tie

*Abb Installation Products, Inc*

Catalog Number	TY523MX
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Black Polyamide (Nylon 6.6) For Temperatures Up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant For Indoor and Outdoor Applications, Length Of 92MM (3.6 Inches), Width Of 2.3MM (0.09 Inches), Thickness Of 1MM (0.04 Inch), Tensile Strength Rating Of 80 Newtons (18 Pounds)
Weight per unit	0.0020 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Tensile Strength	18
------------------	----

### Dimensions and Weight

Length	3.6
Thickness	0.04
Width	0.09

### Descriptions

Description	3.62" "TY-RAP" CABLE TIE
extra long description	ABB TY523MX CBL TIE 18LB 4IN UV BLK
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 92mm (3.6 Inches), Width of 2.3mm (0.09 Inches), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 80 Newtons (18 Pounds)
Product Type	CBL Tie 18LB 4IN Uv BLK 2-PC Dist
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

### Manufacturer Information

Brand	Ty-Rap
GTIN	00786210805085
Manufacturers Part Number	TY523MX
UPC	786210805085

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	100
Weight Per each	0.002