



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY534M 6" "Ty-Rap" Cable Tie

Abb Installation Products, Inc

Catalog Number	TY534M
Manufacturer	Abb Installation Products, Inc
Description	Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, Length Of 152MM (6 Inches), Width Of 3.6MM (0.14 Inch), Thickness Of 1MM (0.04 Inches), Tensile Strength Rating Of 177 Newtons (40 Pounds), #8 Screw For Mounting
Weight per unit	0.0020 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	40:180
------------------	--------

Dimensions and Weight

Length	6
Thickness	0.04
Width	0.14

Descriptions

Description	6" "TY-RAP" CABLE TIE
extra long description	ABB TY534M CBL TIE 40LB 6IN NAT NYL
Long Description	Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 152mm (6 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1mm (0.04 Inches), Tensile Strength Rating of 177 Newtons (40 pounds), #8 Screw for Mounting
Product Type	CBL Tie 40LB 6IN Nat Nyl MTG Hole
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210807003
Manufacturers Part Number	TY534M
UPC	786210807003

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Integrated Mounting Hole



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

minimum qty 100

Packaging

Carton 100

Package 500

Weight Per each 0.002

Uses, Certifications, and Standards

standard UL E49405