



**MILBANK**  
ENERGY AT WORK

## U227MTB-P



Catalog Number	U227MTB-P	Mounting	Surface Mount
Marketing Product Description	7 Terminal Ring Type Small Closing Plate Link Bypass 1-200 Ampere Main Pullout	Enclosure	G90 Galvanized Steel with Powder Coat Finish
UPC	784572135284	Jaw Quantity	7 Terminal
Length (IN)	5.938	Bypass Type	Link Bypass
Width (IN)	22.125	Number of Meter Positions	1 Position
Height (IN)	30	Equipment Ground	Ground Lug
Brand Name	Milbank	Hub Opening	Small Closing Plate
Type	Ring Type Meter Socket	Line Side Wire Range	6 AWG - 250 kcmil
Application	Meter Socket With Main	Load Side Wire Range	1 AWG - 300 kcmil
Standard	UL Listed;Type 3R	Number Of Receptacles	0
Voltage Rating	Up to 240 Volts Alternating Current		
Amperage Rating	200 Continuous Ampere		
Phase	3 Phase		
Frequency Rating	60 Hertz		
Size	5.938L x 22.125W x 30H		
Number Of Cutouts	1		
Cutout Size	One 200 Ampere Main Fuse Pull Out Switch		
Cable Entry	Overhead or Underground		
Terminal	Single Mechanical		
Insulation	Fiberglass with Resin		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.