

U2864-X-KK-5T



Catalog Number	U2864-X-KK-5T
Marketing Product Description	5 Terminal Ringless Large Closing Plate Horn Bypass 4 Position 4-200 Ampere Main Breaker Provision Vertical
UPC	784572153158
Length (IN)	4.844
Width (IN)	36
Height (IN)	29
Brand Name	Milbank
Type	Ringless Meter Socket
Application	Meter Socket With Main
Standard	UL Listed;Type 3R
Voltage Rating	Up to 240 Volts Alternating Current
Amperage Rating	200 Continuous Ampere
Phase	1 Phase
Frequency Rating	60 Hertz
Size	4.844L x 36W x 29H
Number Of Cutouts	0
Cutout Size	Breaker Provision
Cable Entry	Overhead or Underground
Terminal	3/8 Inch Stud
Insulation	Glass Polyester

Mounting	Surface Mount
Enclosure	G90 Galvanized Steel with Powder Coat Finish
Jaw Quantity	5 Terminal
Bypass Type	Horn Bypass
Number of Meter Positions	4 Positions
Equipment Ground	Ground Lug
Hub Opening	Large Closing Plate
Number Branch Circuits	4
Number Of Receptacles	0

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.