




MILBANK[®]
ENERGY AT WORK

U3936-R



Catalog Number	U3936-R	Jaw Quantity	7 Terminal
Marketing Product Description	7 Terminal Ringless Large Hub Open Lever Bypass Tall Shell	Bypass Type	Lever Bypass
UPC	784572274310	Number of Meter Positions	1 Position
Length (IN)	4.844	Equipment Ground	Grounding Stud
Width (IN)	13	Hub Opening	Large Hub Opening
Height (IN)	38.75	Number Of Receptacles	0
Brand Name	Milbank		
Type	Ringless Meter Socket		
Application	Meter Socket		
Standard	UL Listed;Type 3R		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	320 Continuous Ampere		
Phase	3 Phase		
Frequency Rating	60 Hertz		
Size	4.844L x 13W x 38.75H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead or Underground		
Terminal	3/8 Inch Stud		
Insulation	Glass Polyester		
Mounting	Surface Mount		
Enclosure	G90 Galvanized Steel with Powder Coat Finish		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.