



Catalog Number: U5240-O-200S
Item Description: 200A RT MTR DB PED
UPC Code: 784572275928

Brand Name: Milbank
Type: Ring Type Metered Power Supply Unit
Special Features: 4 Terminal, Plain Top, Ground Bar, No Bypass, Single Power Head, 4 Branch Circuits
Application: Mobile Home Power
Standard: UL Listed
Voltage Rating: Up to 240 Volts Alternating Current
Amperage Rating: 200 Ampere Continuous
Wattage: Not Applicable
Frequency Rating: 60 Hertz
Phase: 1 Phase
Number of Receptacles: 0
Control: One 200 Ampere Main Breaker
Material: G90 Galvanized Steel with Powder Coat Finish
Mounting: Pedestal Mount
Cable Size: 6 AWG to 350 KCMIL
Enclosure: Type 3R



Additional Specifications: Number of Main Breakers:1
Main Breaker Size:200 Ampere Main Breaker

Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.



Catalog Number: U5240-O-200S
Item Description: 200A RT MTR DB PED
UPC Code: 784572275928

Brand Name: Milbank
Type: Ring Type Metered Power Supply Unit
Special Features: 4 Terminal, Plain Top, Ground Bar, No Bypass, Single Power Head, 4 Branch Circuits
Application: Mobile Home Power
Standard: UL Listed
Voltage Rating: Up to 240 Volts Alternating Current
Amperage Rating: 200 Ampere Continuous
Wattage: Not Applicable
Frequency Rating: 60 Hertz
Phase: 1 Phase
Number of Receptacles: 0
Control: One 200 Ampere Main Breaker
Material: G90 Galvanized Steel with Powder Coat Finish
Mounting: Pedestal Mount
Cable Size: 6 AWG to 350 KCMIL
Enclosure: Type 3R



Additional Specifications: Number of Main Breakers:1
Main Breaker Size:200 Ampere Main Breaker

Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.