



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

UAG12 1/2" Ua Sealtite Conduit, Bonded UI 100'

Southwire Company

| | |
|------------------|---|
| Catalog Number | UAG12 |
| Manufacturer | Southwire Company |
| Description | Liquidtight Flexible Conduit, 1/2 In Trade Size, 0.82 to 0.84 In Conduit Outer Diameter, 0.622 to 0.642 In Conduit Inner Diameter, TITAN2(TM) UI Style, 100 FT Length, Jacket: Thermoplastic;Core: Steel, Hot Dip Galvanized, Gray, 4 In Bend Radius, -67 °F Operating Temperature, +176 °F Operating Temperature, 30 LB/100 FT |
| Weight per unit | 0.3000 (lbs/ft) |
| Product Category | Liquid Tight Conduit |

Features

| | |
|------------------|-----|
| outside diameter | 830 |
|------------------|-----|

Descriptions

| | |
|------------------------|--|
| Description | 1/2" UA SEALTITE CONDUIT, BONDED UL 100' |
| extra long description | SWC 55082603 Titan2 Type UL Liquidt |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00032886042317 |
| UPC | 032886042317 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------|
| Category Description | Liquid Tight |
| Type | LTM-UL |

Packaging

| | |
|-----------------|-----|
| Carton | 100 |
| Weight Per foot | 0.3 |