




**MILBANK**<sup>®</sup>  
ENERGY AT WORK

## UAP5024-XL



Catalog Number	UAP5024-XL	Mounting	Surface Mount
Marketing Product Description	4 Terminal Ringless Small Closing Plate 12 Branch Circuit Aluminum Painted	Enclosure	Aluminum with Powder Coat Finish
UPC	784572316164	Jaw Quantity	4 Terminal
Length (IN)	4.5	Bypass Type	No Bypass
Width (IN)	14.125	Number of Meter Positions	1 Position
Height (IN)	24	Equipment Ground	Ground Bar
Brand Name	Milbank	Hub Opening	Small Closing Plate
Type	Ringless Meter Socket	Line Side Wire Range	6 AWG - 350 kcmil
Application	Meter Socket With Load Center	Number Branch Circuits	12
Standard	UL Listed;Type 3R	Number Of Receptacles	0
Voltage Rating	Up to 240 Volts Alternating Current		
Amperage Rating	200 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	4.5L x 14.125W x 24H		
Number Of Cutouts	0		
Cutout Size	Breaker Provision		
Cable Entry	Overhead or Underground		
Terminal	Lay in		
Insulation	Glass Polyester		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.