

# Eaton UASTS61C224CH

Catalog Number: UASTS61C224CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, Six-jaw, 1-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

## General specifications



Photo is representative

### Product Name

Eaton meter socket

### UPC

786685216386

### Product Height

20 in

### Product Weight

15 lb

### Certifications

UL Listed

### Catalog Number

UASTS61C224CH

### Product Length/Depth

4.359 in

### Product Width

12 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Product specifications

### Type

Instrument rated socket

### Amperage Rating

20A

### Feed type

Top/bottom

### Number of jaws

Six-jaw

### Phase

Single-phase

### Enclosure material

Aluminum

### Number of wires

Three-wire

### Hub type

3-5/16 in hub cover plate

### Security

Ringless

### Voltage rating

600 V

### Accessories

Factory wired test switch

### Number of sockets

1

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - UASTS61C224CH](#)