

Eaton UASTS61C224CH

Catalog Number: UASTS61C224CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, Six-jaw, 1-ph, Factory wired test switch, Gnd conn (#14-#2 Cu), Al, Triplex, 3-wire, Ringless, 600 Vac

General specifications



Photo is representative

Product Name

Eaton meter socket

UPC

786685216386

Product Height

20 in

Product Weight

15 lb

Certifications

UL Listed

Catalog Number

UASTS61C224CH

Product Length/Depth

4.359 in

Product Width

12 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

defaultTaxonomyAttributeLabel

Type

Instrument rated socket

Amperage Rating

20A

Feed type

Top/bottom

Number of jaws

Six-jaw

Phase

Single-phase

Enclosure material

Aluminum

Number of wires

Three-wire

Hub type

3-5/16 in hub cover plate

Security

Ringless

Voltage rating

600 V

Accessories

Factory wired test switch

Number of sockets

1

Resources

Brochures

[Single Meter Sockets](#)

Drawings

[Dimensional Drawing - SKT/SW 20A 6T FW HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UASTS61C224CH](#)