

PRODUCT INFORMATION

UNDERCABINETS

T5
T8



Intended Use
Ideal for use in school, display or residential applications.

Separate, hingeable service tray for easy installation and maintenance.

Construction
Trim, low-profile design.

FCC part 18 for commercial and residential applications.

Snap-fit, shatter-resistant, milk-white diffuser.

Energy Star® qualified.

Rocker switch and paint-after-fabrication standard.



CONTRACTOR
SELECT

ORDERING INFORMATION

CATALOG NUMBER	NUMBER OF LAMPS	LENGTH	WATTAGE	NUMBER OF BALLAST	VOLTAGE	BALLAST	ENERGY STAR® QUALIFIED	LAMP INCLUDED	LAMP TYPE
UC512	1	12"	8W	1	120	Electronic, instant start	Y	Y	Preheat T5
UC521	1	21"	13W	1	120	Electronic, instant start	Y	Y	Preheat T5
UC524	2	24"	8W	1	120	Electronic, instant start	Y	Y	Preheat T5
UC533	2	33"	One 8W & one 13W	1	120	Electronic, instant start	Y	Y	Preheat T5
UC542	2	42"	13W	1	120	Electronic, instant start	Y	Y	Preheat T5
UC818	1	18"	15W	1	120	Electronic, instant start	Y	N	T8
UC824	1	24"	17W	1	120	Electronic, instant start	Y	N	T8
UC836	1	36"	25W	1	120	Electronic, instant start	Y	N	T8
UC848	1	48"	32W	1	120	Electronic, instant start	Y	N	T8

ADDITIONAL INFORMATION

For additional product information, visit www.lithonia.com.

Drawings are for dimensional detail only and may not represent actual mechanical configuration. Dimensions are shown in inches (centimeters) unless otherwise noted.

