

PRODUCT INFORMATION

RAYZER

Modular LED Lighting System

**Intended Use**

Provides task or accent lighting in commercial, retail, hospitality and residential applications. Ideal for use under and over cabinets, display cases, task lighting, office lighting, coves and utility/work areas.

Features

- Replaces up to a 17W T8
- Durable aluminum construction in a low-profile design. Can be plugged in or direct-wired (splice box and 24" connector cord required for direct-wiring)

- Up to 80% of energy savings vs. fluorescent and xenon
- Multiple installation options
- Linkable functionality
- Slim profile - only 1/2" in height
- Requires 24V step down transformer kit (sold separately)
- Available in 9", 12", 18" and 24" lengths

Listings

cUL Listed to U.S. and Canadian safety standards.



ORDERING INFORMATION

Specifications subject to change.

Example: RAZ18

Series	Options
RAZ9 9" length - 3 LEDs	Consult factory.
RAZ12 12" length - 4 LEDs	
RAZ18 18" length - 6 LEDs	
RAZ24 24" length - 8 LEDs	

ADDITIONAL INFORMATION

For additional product information, visit www.lithonia.com.

ACCESSORIES/REPLACEMENT PARTS

RAZTRANS24 120	24V transformer - 120V power source
RAZTRANS24 MVOLT	24V transformer- Multi-Volt power source
RAZDIM	Step dimmer with remote touch pad
RAZ CC121	121" Linking cord (fixture to fixture)
RAZ CC24	24" linking cord (fixture to fixture)
RAZ CC3	3" linking cord (fixture to fixture)
RAZLVCC	Low voltage linking cord (cord to cord)
RAZ ERC	End row connector
RAZ PHD	Power hub distributor
RAZ INLS26	In-line power switch
UCD JB	Splice box - white (required for direct wire)
UCD JB BL	Splice box - black (required for direct wire)
UC ERC24 R12	24" connector cord - white (required for direct wire)
UC ERC24 BL	24" connector cord - black (required for direct wire)

Specifications

Length: RAZ9 - 9-1/4 (23.5)
RAZ12 - 12-1/4 (31.1)
RAZ18 - 18-1/4 (46.4)
RAZ24 - 24-1/4 (61.6)
Width: 1-1/4 (3.18)
Height: 1/2" (1.27)

All dimensions are inches (centimeters)

Notes

- 1 Lamps not included.
- 2 Use with non-dimmable switches only.

PRODUCT INFORMATION

RAYZER

Modular LED Lighting System

**Intended Use**

Provides task or accent lighting in commercial, retail, hospitality and residential applications. Ideal for use under and over cabinets, display cases, task lighting, office lighting, coves and utility/work areas.

Features

- Replaces up to a 17W T8
- Durable aluminum construction in a low-profile design. Can be plugged in or direct-wired (splice box and 24" connector cord required for direct-wiring)

- Up to 80% of energy savings vs. fluorescent and xenon
- Multiple installation options
- Linkable functionality
- Slim profile - only 1/2" in height
- Requires 24V step down transformer kit (sold separately)
- Available in 9", 12", 18" and 24" lengths

Listings

cUL Listed to U.S. and Canadian safety standards.



ORDERING INFORMATION

Specifications subject to change.

Example: RAZ18

Series

RAZ9	9" length - 3 LEDs
RAZ12	12" length - 4 LEDs
RAZ18	18" length - 6 LEDs
RAZ24	24" length - 8 LEDs

Options

Consult factory.

ADDITIONAL INFORMATION

For additional product information, visit www.lithonia.com.

ACCESSORIES/REPLACEMENT PARTS

RAZTRANS24 120	24V transformer - 120V power source
RAZTRANS24 MVOLT	24V transformer- Multi-Volt power source
RAZDIM	Step dimmer with remote touch pad
RAZ CC121	121" Linking cord (fixture to fixture)
RAZ CC24	24" linking cord (fixture to fixture)
RAZ CC3	3" linking cord (fixture to fixture)
RAZLVCC	Low voltage linking cord (cord to cord)
RAZ ERC	End row connector
RAZ PHD	Power hub distributor
RAZ INLS26	In-line power switch
UCD JB	Splice box - white (required for direct wire)
UCD JB BL	Splice box - black (required for direct wire)
UC ERC24 R12	24" connector cord - white (required for direct wire)
UC ERC24 BL	24" connector cord - black (required for direct wire)

Specifications

Length: RAZ9 - 9-1/4 (23.5)
RAZ12 - 12-1/4 (31.1)
RAZ18 - 18-1/4 (46.4)
RAZ24 - 24-1/4 (61.6)
Width: 1-1/4 (3.18)
Height: 1/2" (1.27)

All dimensions are inches (centimeters)

Notes

- 1 Lamps not included.
- 2 Use with non-dimmable switches only.