



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UCS5075 1/2"-3/4" 1H Universal Clampback Strap

Bridgeport Fittings

| | |
|------------------|---|
| Catalog Number | UCS5075 |
| Manufacturer | Bridgeport Fittings |
| Description | One Piece Clamp Back and Strap Combination, 1 Hole, Steel, 1/2" - 3/4" Trade Size. Patent Pending |
| Weight per unit | 0.1080 (lbs/each) |
| Product Category | Steel One Hole Emt Straps |

Features

| | |
|----------|-------------------|
| Material | ZINC PLATED STEEL |
| media | Yes |

Descriptions

| | |
|------------------------|---|
| Description | 1/2"-3/4" 1H UNIVERSAL CLAMPBACK STRAP |
| extra long description | BPT UCS-5075 1/2" - 3/4" UNIVERSAL |
| Features | Problem Solver: One-piece clamp back and strap design holds everything! |
| Long Description | One piece clamp back and strap combination, 1 hole, Steel, 1/2" - 3/4" Trade Size. Patent Pending |
| Product Type | 1/2" - 3/4" Universal Strap |
| Special Features | Trade size 1/2" - 3/4" steel, 1 hole, one piece clamp back and strap combination. |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747029324 |
| Manufacturers Part Number | UCS5075 |
| UPC | 781747029324 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | RIGID STRAPS & CLAMPBACKS |
| Type | Clamp Straps |

Packaging

| | |
|-----------------|-------|
| Carton | 50 |
| Package | 250 |
| Weight Per each | 0.108 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

The one piece clamp back and strap secures both cable and conduit. The UCS-5075 secures 1/2" and 3/4" EMT, Rigid, IMC, PVC/Polyolefin Coated Rigid, PVC/Polyolefin Coated IMC, Metallic Liquid Tight, Nonmetallic Liquid Tight, FMC, and Schedule 40 and Schedule 80 PVC conduit, as well as .710" 0 to 1.10" 0 steel and aluminum AC/MC cable.

standard

UL