



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UF2 Splice Kit UF2 Stretched *Minnesota Mining (3M)*

Catalog Number	UF2
Manufacturer	Minnesota Mining (3M)
Description	3M™ Scotchlok™ Uf Series Standard Splice Kits Include All The Accessories Required to Offer A Reliable, Moisture Proof Electrical Connection For Type Uf B Underground Feeders. These Kits Are Suitable to Use On 600V Rated, Flat, Non Shielded Uf Cables.
Weight per unit	0.7093 (lbs/each)
Product Category	Splicing & Terminating Kits

Descriptions

Description	SPLICE KIT UF2 STRETCHED
extra long description	3M 7000132747 3M™ Splice Kit UF
Features	The Splice Kit UF Series consists of a connector insulation assembly and a heat shrink tube. The connector assembly contains four cylindrical set screw connectors separated by a piece of vinyl insulation. The heat shrink tube is a heavy wall, adhesive lined tube and is UL Listed and RoHS 2011/65/EU Compliant. It withstands a temperature range of 67 to 230 degrees F (55 to 110 degrees C).
Long Description	3M™ Scotchlok™ UF Series Standard Splice Kits include all the accessories required to offer a reliable, moisture proof electrical connection for type UF B underground feeders. These kits are suitable to use on 600V rated, flat, non shielded UF cables.
Product Type	3M™ Splice Kit Uf

Manufacturer Information

Brand	3M
GTIN	00054007429210
Manufacturers Part Number	7000132747
UPC	054007429210

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	Splice Kit

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	6
Weight Per each	0.7093



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

moisture proof electrical connection for type U.F.-B underground feeder cable rated for 600 volts (Copper Wire Only) ranging from #14/3 without ground wire up to #8/3 with ground wire.