



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UGR020231 20A125V Recpt

Hubbell--Killark

Catalog Number	UGR020231
Manufacturer	Hubbell--Killark
Description	Ugr Series - Aluminum 20 Amp 125V Interchangeable Blade Style Receptacle- 2P 3W Circuit - Nema Configuration 5-20R
Weight per unit	1.6 (lbs/each)
Product Category	Wiring Devices

Features

amperage rating	20
Number of Wires	3
Poles	2
Voltage Rating	125V

Dimensions and Weight

Depth	4-3/16
Height	6
Width	3

Descriptions

Description	20A125V RECPT
extra long description	KLRK UGRO-20231 ACCEPTOR RECEPTACLE
Long Description	UGR SERIES - ALUMINUM 20 AMP 125V INTERCHANGEABLE BLADE STYLE RECEPTACLE- 2P 3W CIRCUIT - NEMA CONFIGURATION 5-20R
Product Type	Acceptor Receptacle 120V
Special Features	All external hardware is 316 stainless steel to provide low maintenance and long life. Factory sealed chamber in UGR receptacle contains switch's arcing components. No additional external seals are required, except in Group B applications. Receptacles are

Manufacturer Information

Brand	KILLARK
GTIN	00783936991979
Manufacturers Part Number	UGRO-20231
UPC	783936991979

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Aluminum interchangeable blade style receptacle and box

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 1.6

Uses, Certifications, and Standards

Application Petroleum refineries, chemical plants, wet/damp areas, corrosive environments, petroleum plants, grain elevators/feed mills, flour and feed mills, and indoor or outdoor locations

environmental conditions Wet and hazardous locations

nema rating NEMA 3, 7BCD, 9FG

standard UL, CSA