

Eaton UHTRS101BE

Catalog Number: UHTRS101BE

Eaton meter socket, 1-pos resi service, 125 A, Over, 3-5/16 inch hub open, #8-2/0 AWG, 4-jaw, 1-ph, #8-2/0 AWG, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac



General specifications

Product Name

Eaton meter socket

Catalog Number

UHTRS101BE

UPC

786685217734

Product Length/Depth

3.61 in

Product Height

11.05 in

Product Width

8.22 in

Product Weight

6.7 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Product specifications

Type

Single-position residential service

Amperage Rating

125A

Feed type

Overhead

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

NY : Central Hudson Gas & Electric (CHG&E)

OH : Dayton Power and Light (DP&L)

MD : First Energy (Potomac Edison)

VA : First Energy (Potomac Edison)

WV : First Energy (Mon Power)

NJ : First Energy (Jersey Central Power and Light)

OH : First Energy (Ohio Edison, Toledo Edison, The Illuminating Company)

PA : First Energy (Allegheny Power, MET ED, Penelec, West Penn Power)

WI : Madison Gas and Electric (MGE)

IN : Northern Indiana Public Service Company (NIPSCO)

WI : WE Energies / Wisconsin Public Service (WPS)

NY : Rochester Gas & Electric (RG&E)

NY : New York State Electric & Gas (NYSEG)

Line

#8-2/0 AWG

Load

#8-2/0 AWG

Number of wires

Three-wire

Hub type

3-5/16 in hub opening

Security

Ringless

Voltage rating

600 V

Resources

Catalogs

[Residential and Light Commercial, Metering Products, Volume 1 Tab 4](#)

Specifications and datasheets

[Eaton Specification Sheet - UHTRS101BE](#)

Bypass

Horn

Number of sockets

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia