



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNL105 1/2" Female/Male 90D Elbow *Crouse-Hinds*

Catalog Number	UNL105
Manufacturer	Crouse-Hinds
Description	90° Elbow, 1/2 to 1/2 In Trade Size, Uni Model, Angle Shape, Electro Galvanized and Aluminum Acrylic Paint, Female to Male Connection, 2-11/16 In Length, 1-17/32 In Width, 1-17/32 In Diameter, 0.58 LB
Weight per unit	0.5800 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	2.6900 IN X 1.5300 IN X 2.0000 IN

Descriptions

Description	1/2" FEMALE/MALE 90D ELBOW
extra long description	CRS-H UNL105 1/2 NPT 90 DEGREE ANG
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274647203
UPC	782274647203

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Package	10
Weight Per each	0.58

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	Condulet UL 886, CSA C22.2