



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



UNL205 3/4" Female/Male 90D Elbow

Crouse-Hinds

Catalog Number	UNL205
Manufacturer	Crouse-Hinds
Description	90° Elbow, 3/4 to 3/4 In Trade Size, Unl Model, Angle Shape, Electro Galvanized and Aluminum Acrylic Paint, Female to Male Connection, 2-7/8 In Length, 1-13/16 In Width, 1-13/16 In Diameter, 0.75 LB
Weight per unit	0.7500 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	2.8800 IN X 1.8100 IN X 2.0000 IN

Descriptions

Description	3/4" FEMALE/MALE 90D ELBOW
extra long description	CRS-H UNL205 3/4 NPT 90 DEGREE ANG
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274647302
UPC	782274647302

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Union

Packaging

Carton	1
Package	10
Weight Per each	0.75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Condulet
standard	UL 886, CSA C22.2