

# Eaton UNRRS101BEUSE

Catalog Number: UNRRS101BEUSE

Eaton meter socket, 3-5/16 Hub Opening, 125A, Overhead, 3-5/16 Hub Opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V

## General specifications



### Product Name

Eaton meter socket

### Catalog Number

UNRRS101BEUSE

### UPC

786685217840

### Product Length/Depth

3.6 in

### Product Height

11.05 in

### Product Width

8.22 in

### Product Weight

7.35 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

3-5/16 Hub Opening

### Amperage Rating

125A

### Feed type

Overhead

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

TX : CenterPoint Energy (HL&P/Reliant)

### Line

#8-2/0 kcmil

### Load

#8-2/0 kcmil

### Enclosure material

16 GA GALV STEEL

### Number of wires

Three-wire

### Hub type

3-5/16 hub opening

### Security

Ring

### Voltage rating

600 V

### Number of sockets

1

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - UNRRS101BEUSE



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton UNRRS101BEUSE

Catalog Number: UNRRS101BEUSE

Eaton meter socket, 3-5/16 Hub Opening, 125A, Overhead, 3-5/16 Hub Opening, #8-2/0 kcmil, Four-jaw, Single-phase, #8-2/0 kcmil, Sockets:1, Three-wire, Ring, 600V



## General specifications

### Product Name

Eaton meter socket

### Catalog Number

UNRRS101BEUSE

### UPC

786685217840

### Product Length/Depth

3.6 in

### Product Height

11.05 in

### Product Width

8.22 in

### Product Weight

7.35 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## Product specifications

### Type

3-5/16 Hub Opening

### Amperage Rating

125A

### Feed type

Overhead

### Number of jaws

Four-jaw

### Phase

Single-phase

### Utility approvals

TX : CenterPoint Energy (HL&P/Reliant)

### Line

#8-2/0 kcmil

### Load

#8-2/0 kcmil

### Enclosure material

16 GA GALV STEEL

### Number of wires

Three-wire

### Hub type

3-5/16 hub opening

### Security

Ring

### Voltage rating

600 V

### Number of sockets

1

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - UNRRS101BEUSE



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)