



WIREMOLD TEMPORARY POWER TAP CORD-ENDED PLUGMOLD® 2000 UNITS

INSTALLATION INSTRUCTIONS

WARNING: For maximum safety, this Wiremold Temporary Power Tap is equipped with a grounding type plug (3-prong) for use *only* with grounding type receptacles. Modification of the plug to allow its use in non-grounding receptacles voids the warranty and may lead to electrical shock.

1. Be sure the proposed location for the Wiremold Temporary Power Tap is close enough to an existing wall outlet to be reached by the cordset.
2. Line up and locate where to install the mounting clips. For best results, snap a chalkline or draw a guide line. When unit is to be installed under an overhanging surface, such as under a cupboard or shelf, allow at least 1/2" [12.7mm] clearance between the top side of the unit and the overhanging surface. This will avoid interference with plug caps of the cords on tools, appliances, etc. to be powered by the strip.
3. Install mounting clips. **IMPORTANT** – if the flat head screws furnished are *not* used, the substitute fasteners must also be of the flat head type, or the unit will not seat securely in the mounting clips.
4. Snap temporary power tap into mounting clips, and plug cordset into the wall outlet.

Wiremold Electrical Systems conform to and should be installed and properly grounded in compliance with requirements of the current National Electrical Code, Canadian Electrical Code or codes administered by local authorities.

All electrical products may represent possible shock or fire hazard if improperly installed or used. Wiremold electrical products are UL Listed to U.S. and Canadian safety standards, made for interior use only, and should be installed in conformance with current local and/or the National Electrical Code.
