

# Specifications



Photo is representative



## Eaton V48M28T15

Eaton general purpose ventilated transformer, Dry Type Distribution, DT-3, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings, Frame: 912B, uses WS38

### General specifications

|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton General purpose ventilated transformer   |
| <b>CATALOG NUMBER</b>       | V48M28T15  |
| <b>UPC</b>                  | 786680035234   |
| <b>PRODUCT LENGTH/DEPTH</b> | 16.5 in  |
| <b>PRODUCT HEIGHT</b>       | 32.02 in   |
| <b>PRODUCT WIDTH</b>        | 23 in  |
| <b>PRODUCT WEIGHT</b>       | 181 lb   |
| <b>WARRANTY</b>             | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>CERTIFICATIONS</b>       | UL Listed  |



Powering Business Worldwide

## Physical Attributes

|               |                                      |
|---------------|--------------------------------------|
| COIL MATERIAL | Aluminum                             |
| DESIGN        | DT-3                                 |
| FRAME         | 912B                                 |
| TAP SIZE      | 2 at +2.5% FCAN, 4 at -2.5%<br>FCBN  |
| TYPE          | Dry Type Distribution<br>Transformer |

## Miscellaneous

|               |      |
|---------------|------|
| WEATHERSHIELD | WS38 |
|---------------|------|

## Performance Ratings

|                   |             |
|-------------------|-------------|
| FREQUENCY RATING  | 60 Hz       |
| KVA RATING        | 15 kVA      |
| PRIMARY VOLTAGE   | 480 V       |
| SECONDARY VOLTAGE | 208Y/120 V  |
| TEMPERATURE RISE  | 150 °C rise |

## Resources

|                               |  |
|-------------------------------|--|
| CATALOGS                      | <a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a> |
| SPECIFICATIONS AND DATASHEETS | <a href="#">Eaton Specification Sheet - V48M28T15</a>                  |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton V48M28T15

Eaton general purpose ventilated transformer, Dry Type Distribution, DT-3, Three-phase, PV: 480V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 208Y/120V, 150°C, 15 kVA, Al windings, Frame: 912B, uses WS38

### General specifications

|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton General purpose ventilated transformer   |
| <b>CATALOG NUMBER</b>       | V48M28T15  |
| <b>UPC</b>                  | 786680035234   |
| <b>PRODUCT LENGTH/DEPTH</b> | 16.5 in  |
| <b>PRODUCT HEIGHT</b>       | 32.02 in   |
| <b>PRODUCT WIDTH</b>        | 23 in  |
| <b>PRODUCT WEIGHT</b>       | 181 lb   |
| <b>WARRANTY</b>             | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>CERTIFICATIONS</b>       | UL Listed  |



Powering Business Worldwide

## Physical Attributes

|                      |                                      |
|----------------------|--------------------------------------|
| <b>COIL MATERIAL</b> | Aluminum                             |
| <b>DESIGN</b>        | DT-3                                 |
| <b>FRAME</b>         | 912B                                 |
| <b>TAP SIZE</b>      | 2 at +2.5% FCAN, 4 at -2.5%<br>FCBN  |
| <b>TYPE</b>          | Dry Type Distribution<br>Transformer |

## Miscellaneous

|                      |      |
|----------------------|------|
| <b>WEATHERSHIELD</b> | WS38 |
|----------------------|------|

## Performance Ratings

|                          |             |
|--------------------------|-------------|
| <b>FREQUENCY RATING</b>  | 60 Hz       |
| <b>KVA RATING</b>        | 15 kVA      |
| <b>PRIMARY VOLTAGE</b>   | 480 V       |
| <b>SECONDARY VOLTAGE</b> | 208Y/120 V  |
| <b>TEMPERATURE RISE</b>  | 150 °C rise |

## Resources

|                                      |  |
|--------------------------------------|--|
| <b>CATALOGS</b>                      | <a href="#">Commercial Distribution, Transformers, Volume 2, Tab 2</a> |
| <b>SPECIFICATIONS AND DATASHEETS</b> | <a href="#">Eaton Specification Sheet - V48M28T15</a>                  |

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

