



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VAPOR1B040UNVD84 *Delisted* VAPOR1B/040unvd84048ecgr *Sylvania-Ledvance*

Catalog Number	VAPOR1B040UNVD84
Manufacturer	Sylvania-Ledvance
Description	OBS74376 Vapor Tight 1B, 4 Feet, 40 Watts, 4000K, IP65, 120 277V, 0 10V Dimmable, Etched Lens, Canopy Distribution, Gray Polycarbonate Finish
Weight per unit	6.1 (lbs/each)
Product Category	Led Vapor Tight Lighting

Features

accessories	Chain mount bracket
average life	120000
dimnable	Yes
housing	Polycarbonate (PC)
lumens	5,300
Material	Polycarbonate (PC)
Voltage	120.00 - 277.00 V
Wattage	40.00

Material, Color, and Finish

color rendering index (cri)	>80
color temperature	4000

Descriptions

Description	*DELISTED* VAPOR1B/040UNVD84048ECGR
extra long description	SYL VAPOR1B/040UNVD840/48EC/GR/7437
Long Description	OBS74376 Vapor Tight 1B, 4 feet, 40 watts, 4000K, IP65, 120 277V, 0 10V dimmable, etched lens,canopy distribution, gray polycarbonate finish

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135743764
Manufacturers Part Number	VAPOR1B/040UNVD840/48EC/GR/743
UPC	046135743764

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
----------------------	---

Packaging

Carton	1
Package	4
Weight Per each	6.1275

Uses, Certifications, and Standards

standard	cULus
----------	-------