



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VHBLEDLD118WUNVL 134W Led Highbay 40K 18000LM Dim 120-277V Wide *Cooper Lighting Solutions*

Catalog Number	VHBLEDLD118WUNVL
Manufacturer	Cooper Lighting Solutions
Description	Led High Bay, White Enamel, CRS;Aluminum, 120/277 V Ac, 0.36 A @ 277 V, 160 W, 60000 H Average Life, 18568 LM Brightness (Lumens), 3500 K;4000 K;5000 K, 85, Non Dimmable, Wide Beam Spread, Surface/Chain Mount, 18-27/32 In Length, 14-19/32 In Width, 3-13/16 In Height, 15 LB
Weight per unit	15.0 (lbs/each)
Product Category	Led Highbay Lighting

Features

amperage rating	0.36 (at 277V)
Ballast Type	N/A
Lamp Type	LED

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	VHBLEDLD118WUNV840CD1U
extra long description	CLS VHB-18-W-UNV-L840-CD-U VHB 180

Manufacturer Information

Brand	Cooper Metalux
GTIN	00080083785919
Manufacturers Part Number	VHB-18-W-UNV-L840-CD-U
UPC	080083785919

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	INDUSTRIAL

Packaging

Carton	1
Weight Per each	15

Uses, Certifications, and Standards

Mounting	High Bay
standard	cULus Listed - Damp Location;40 Degree C Ambient Temperature Rating;RoHS Compliant;LM79/LM80 Compliant;DLC Qualified