



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WCOB Orn Twist-On Wire Conn *Nsi Industries*

Catalog Number	WCOB
Manufacturer	Nsi Industries
Description	Twist-On Wire Connector, (1) #18 Awg;(1) #20 Awg Conductor Size, (4) #16 Awg;(1) #20 Awg Conductor Size, Insulated, Thermoplastic Insulation Material, Copper Conductor Material, Orange Insulation Color, +221 °F Operating Temperature, 0.197 In Overall Width, 0.866 In Overall Height, 600 V, 1.48 LB
Weight per unit	1.5 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Thermoplastic
Number of Conductors	1
Voltage Rating	600
Warranty	1 YEAR
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Orange
Finish	Thermoplastic

Dimensions and Weight

Size	H=.866 - W=.500 - ID=.197
------	---------------------------

Descriptions

Description	ORN TWIST-ON WIRE CONN
extra long description	NSI WC-O-B Easy-Twist Orange - 500

Manufacturer Information

GTIN	00662381140227
UPC	662381140227

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Standard Wire Connectors

Availability

minimum qty	500
-------------	-----

Packaging

Carton	1
Package	500
Weight Per each	1.48



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C
Temperature Rating	105 C